



| | |
|--------------------|----------------|
| Thread code:UQBN | |
| Thread type | ACME |
| Major diameter(mm) | 9.779...10.033 |
| Minor diameter(mm) | 7.938...8.065 |
| Lead | 1.5875 |
| Pitch | 1.5875 |
| Starts | 1 |

| | | | | | | | |
|----------------------------------|-------------|------|------|------------------------------|--|---------------------|--|
| General tolerances ISO 2768-m | | | | Work piece edges DIN 6784 | | Scale: | |
| | | | | | | Material: POM | |
| | | | | | | Surface: | |
| | | | | Datum | | Name | |
| | | | | DRN 2020/4/23 | | X T | |
| | | | | CHKD 2020/4/23 | | GYQ | |
| | | | | APVD 2020/4/23 | | P.R. | |
| | | | | | | External linear nut | |
| | | | | | | | |
| | | | | | | A3 | |
| Rev | Description | Date | Name | | | | |