



Thread code:UGAQ	
Thread type	ACME
Major diameter [mm]	4.636...4.763
Minor diameter [mm]	3.579...3.874
Lead	0.635
Pitch	0.635
Starts	1
Thread per inch	40

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )	
				 <b>Nanotec</b> <sup>®</sup> PLUG & DRIVE			Name	Date	THREADED SPINDLE
B	-	21.07.22	X T				DRN	X T	
A	-	09.12.20	X T				CHKD	GYQ	12.04.2018
REV	DESCRIPTION	DATE	DRN				APVD	P.R	12.04.2018