



Thread code:UGFC	
Thread type	ACME
Major diameter [mm]	4.636...4.763
Minor diameter [mm]	2.868...3.239
Lead	5.08
Pitch	1.27
Starts	4
Thread per inch	20

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )	
				 <b>Nanotec</b> <sup>®</sup> PLUG & DRIVE			Name	Date	THREADED SPINDLE
B	-	21.07.22	X T				DRN	X T	
A	-	09.12.20	X T				CHKD	GYQ	13.03.2018
REV	DESCRIPTION	DATE	DRN				APVD	P.R	13.03.2018