



Thread code UKAS	
Thread type	ACME
Major diameter [mm]	6.223...6.350
Minor diameter [mm]	4.983...5.301
Lead	0.79375
Pitch	0.79375
Starts	1
Thread per inch	32

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)		
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE	
B	-	25.07.22	X T				DRN	L W		12.04.2018
A	-	09.12.20	X T				CHKD	GYQ	12.04.2018	SCREW-AAA-UKAS-1000
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	12.04.2018	