



Thread code UGAQ	
Thread type	ACME
Major diameter [mm]	4.636...4.763
Minor diameter [mm]	3.579...3.874
Lead	0.635
Pitch	0.635
Starts	1
Thread per inch	40

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)		
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE	
B	-	21.07.22	X T				DRN	L W		12.04.2018
A	-	09.12.20	X T				CHKD	GYQ	12.04.2018	SCREW-ABA-UGAQ-200
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	12.04.2018	