



Thread code UIAP	
Thread type	ACME
Major diameter [mm]	5.431...5.558
Minor diameter [mm]	4.402...4.694
Lead	0.6096
Pitch	0.6096
Starts	1
Thread per inch	41.67

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (±1.4570)	
				 <b>Nanotec</b> PLUG & DRIVE			Name	Date	THREADED SPINDLE
B	-	22.07.22	X T				DRN	L W	
A	-	09.12.20	X T				CHKD	GYQ	10.04.2018
REV	DESCRIPTION	DATE	DRN	APVD	P.R.	10.04.2018			