



| Thread code UKDE    |               |
|---------------------|---------------|
| Thread type         | ACME          |
| Major diameter [mm] | 6.223...6.350 |
| Minor diameter [mm] | 4.107...4.509 |
| Lead                | 3.175         |
| Pitch               | 1.5875        |
| Starts              | 2             |
| Thread per inch     | 16            |

|     |             |          |     |   |                                       |  |                                  |   |                  |                    |
|-----|-------------|----------|-----|---|---------------------------------------|--|----------------------------------|---|------------------|--------------------|
|     |             |          |     |   | Surface specification<br>DIN ISO 1302 | General tolerances<br>DIN ISO 2768- mK | Work piece edge<br>DIN ISO 13715 | Scale:<br>Material: SUS303Cu ( $\pm 1.4570$ ) |                  |                    |
|     |             |          |     | <br><b>Nanotec</b> <sup>®</sup><br>PLUG & DRIVE |                                       |  | Name                             | Date  | THREADED SPINDLE |                    |
| B   | -           | 25.07.22 | X T |   |                                       |  | DRN                              | L W   |                  | 12.04.2018         |
| A   | -           | 09.12.20 | X T |   |                                       |  | CHKD                             | GYQ   | 12.04.2018       | SCREW-ABA-UKDE-300 |
| REV | DESCRIPTION | DATE     | DRN |   |                                       |  | APVD                             | P.R.  | 12.04.2018       |                    |