



Thread code TJCA	
Thread type	Trapezoid
Major diameter [mm]	5.888...6.000
Minor diameter [mm]	4.444...4.700
Lead	2
Pitch	1
Starts	2
Thread per inch	25,4

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)		
							Name	Date		
B	-	25.07.22	X T				DRN	L W	10.04.2018	THREADED SPINDLE
A	-	09.12.20	X T				CHKD	GYQ	10.04.2018	SCREW-AAA-TJCA-1000
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	10.04.2018	