



Thread code UIEV	
Thread type	ACME
Major diameter [mm]	5.431...5.558
Minor diameter [mm]	3.719...4.084
Lead	4.8768
Pitch	1.2192
Starts	4
Thread per inch	20.83

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (±1.4570)		
				 Nanotec PLUG & DRIVE			Name	Date		
B	-	22.07.22	X T				DRN	X T	18.07.2018	THREADED SPINDLE
A	-	09.12.20	X T				CHKD	GYQ	18.07.2018	
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	18.07.2018	SCREW-AAA-UIEV-1000