



Thread code TJBA	
Thread type	Trapezoid
Major diameter [mm]	5.888...6.000
Minor diameter [mm]	4.465...4.700
Lead	1
Pitch	1
Starts	1
Thread per inch	25.4

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)	
				 Nanotec PLUG & DRIVE			Name	Date	THREADED SPINDLE
B	-	25.07.22	X T				DRN	L W	
A	-	09.12.20	X T				CHKD	GYQ	10.04.2018
REV	DESCRIPTION	DATE	DRN	APVD	P.R.	10.04.2018			