


Thread code TJCA

Thread type	Trapezoid
Major diameter [mm]	5.888...6.000
Minor diameter [mm]	4.444...4.700
Lead	2
Pitch	1
Starts	2
Thread per inch	25.4



Surface specification  
DIN ISO 1302

General tolerances  
DIN ISO 2768- mK

Work piece edge  
DIN ISO 13715

Scale:

Material: SUS303Cu (±1.4570)

B	-	25.07.22	X T
A	-	09.12.20	X T
REV	DESCRIPTION	DATE	DRN



	Name	Date
DRN	L W	10.04.2018
CHKD	GYQ	10.04.2018
APVD	P.R.	10.04.2018

THREADED SPINDLE

SCREW-ABA-TJCA-200