



Thread code UIEV	
Thread type	ACME
Major diameter [mm]	5.431...5.558
Minor diameter [mm]	3.719...4.084
Lead	4.8768
Pitch	1.2192
Starts	4
Thread per inch	20.83

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )		
				 <b>Nanotec</b> <sup>®</sup> PLUG & DRIVE			Name	Date	THREADED SPINDLE	
B	-	22.07.22	X T				DRN	X T		18.07.2018
A	-	09.12.20	X T				CHKD	GYQ	18.07.2018	SCREW-ABA-UIEV-200
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	18.07.2018	