



Thread code UIEV	
Thread type	ACME
Major diameter [mm]	5.431...5.558
Minor diameter [mm]	3.719...4.084
Lead	4.8768
Pitch	1.2192
Starts	4
Thread per inch	20.83

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)	
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE
B	-	22.07.22	X T				DRN	X T	
A	-	09.12.20	X T				CHKD	GYQ	18.07.2018
REV	DESCRIPTION	DATE	DRN			APVD	P.R.	18.07.2018	SCREW-ABA-UIEV-300