



Thread code TDBA	
Thread type	Trapezoid
Major diameter [mm]	3.388...3.500
Minor diameter [mm]	1.975...2.200
Lead	1
Pitch	1
Starts	1

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )		
							Name	Date		
							DRN	X T	28.02.2022	THREADED SPINDLE
							CHKD	GYQ	28.02.2022	SCREW-ABA-TDBA-300
A	-	27.05.22	X T				APVD	P.R.	28.02.2022	
REV	DESCRIPTION	DATE	DRN							