



Thread code THCA	
Thread type	Trapezoid
Major diameter [mm]	4.888...5.000
Minor diameter [mm]	3.455...3.700
Lead	2
Pitch	1
Starts	2
Thread per inch	25,4

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)	
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE
A	-	27.05.22	X T				DRN	X T	
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	07.10.2021