



Thread code TSCA	
Thread type	Trapezoid
Major diameter [mm]	9.820...10.000
Minor diameter [mm]	7.191...7.500
Lead	2
Pitch	2
Starts	1
Thread per inch	12.7

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)	
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE
							DRN	X T	
A	-	25.07.22	X T				CHKD	GYQ	29.04.2020
REV	DESCRIPTION	DATE	DRN	APVD	P.R.	29.04.2020			