



Thread code TSGA	
Thread type	Trapezoid
Major diameter [mm]	9.764...10.000
Minor diameter [mm]	6.150...6.500
Lead	6
Pitch	3
Starts	2
Thread per inch	8.467

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )	
				 <b>Nanotec</b> <sup>®</sup> PLUG & DRIVE			Name	Date	
					DRN	X T	29.04.2020	THREADED SPINDLE	
					CHKD	GYQ	29.04.2020		
					APVD	P.R.	29.04.2020	SCREW-AAA-TSGA-1000	
A	-	25.07.22	X T						
REV	DESCRIPTION	DATE	DRN						