



Thread code TSGA	
Thread type	Trapezoid
Major diameter [mm]	9.764...10.000
Minor diameter [mm]	6.150...6.500
Lead	6
Pitch	3
Starts	2
Thread per inch	8.467

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)		
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE	
A	-	25.07.22	X T				DRN	X T		29.04.2020
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	29.04.2020	