



Thread code UQBN	
Thread type	ACME
Major diameter [mm]	9.398...9.525
Minor diameter [mm]	7.257...7.684
Lead	1.5875
Pitch	1.5875
Starts	1
Thread per inch	16

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)		
							Name	Date	THREADED SPINDLE	
A	-	25.07.22	X T				DRN	X T		29.04.2020
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	29.04.2020	