


Wirelist



CONNECTOR M12 terminating resistor Modbus RTU		
M12 / 4-Pole / B-Coding / male / straight		
Contact Resistance	mΩ	≤5
Contact Material	Brass, Gold-Plated	
Contact Carrier Material	TPU	
Connector Body Material	TPU	
Coupling (Nut / Screw)	Zinc, Nickel-Plated	
Protection Class	IP67 (locked Condition)	

GENERAL SPECIFICATION		
Rating Voltage	AC/DC V	200
Insulation resistance	MΩ	≥100
Ambient temperature	-20°C...+80°C	
All materials are RoHS/REACH compliant		

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: ---- kg		
			Date	Name	ZC-M12-4-M-B-MBR-TR	
			Drawn	11.05.2022		Schneid_A
			Reviewed	13.05.2022		Reith_S
			Released	13.05.2022		Reith_S
			Nanotec® PLUG & DRIVE			20001479
REV	Rev. Text	Name	Date	State: Released		Rev: 00
				CONFIDENTIAL		A4 Page 1