


Shaft Diameter D [mm]	Motor Series	Height h ± 0.15 [mm]	Length L ± 0.25 [mm]
3	All Series	2.5	7
4	DF32	3.5	7.7
4	DF45	3.5	14.4
4	DB28	3.5	15
4	All Others	3.5	10.5
5	SC2818, ST2818	4.5	15
5	All Others	4.5	19
6.35	All Others	5.8	16
8	All Others	7.5	16
10	DFA90	9	16
14	All Others	13	32



ISO 8015		ISO 1302		ISO 2768 cK		ISO 13715		Weight: ---- kg	
					Date	Name		Shaft Modification - D-Cut	
				Drawn	31.10.2018	Schneid_A			
				Reviewed	07.11.2018	Knoll_J			
				Released	07.11.2018	Knoll_J			
01	+ DFA90	Schneid_A	28.05.2020			06200168		A4 Page 1	
REV	Rev. Text	Name	Date					State: Released	