



**WHEEL DRIVE SPECIFICATION**

		11 (18225/1681)	16 (3969/256)	20 (7371/368)	26 (6993/272)
Reduction Ratio xx					
No. of Stages		2			
Rated Output Torque	Nm	20.27	22.01	23.03	23.13
Max. Output Torque	Nm	40.54	44.02	46.06	46.26
Rated Input Speed	rpm	3500	3500	3500	3500
Max. Input Speed	rpm	4685	5968	8304	8988
Backlash	°	<30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	%	94	94	94	94
Inertia	10 <sup>-6</sup> kg m <sup>2</sup>	70	37	22	14
Load Capacity	kg	400			
Wheel Material		Vulkollan			
Ambient Temperature	°C	-15...+90			
Protection Class		IP54			



ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: ± 10% 4.1kg
05 updated specifications	Kolev_I	02.05.2024	Date Name	WD16050-56xx-60X
04 sun depth changed	Kolev_I	31.01.2024	Drawn 09.09.2019 Rehse_P	
03 Load capacity updated	Micheli_M	30.06.2020	Reviewed 13.09.2019 Naubert_A	
02 specifications updated	Micheli_M	31.03.2020	Released 13.09.2019 Naubert_A	
01 First Released				
REV Rev. Text	Name	Date	06200354	
			State: Released	
			Rev: 05	
			CONFIDENTIAL	

Scale: 1 : 2  
A3 Page 1

