



WHEEL DRIVE SPECIFICATION					
Reduction Ratio xx		11 (18225/1681)	16 (3969/256)	20 (7371/368)	26 (6993/272)
No. of Stages		2			
Rated Output Torque	Nm	20.27	22.01	23.03	23.13
Max. Output Torque	Nm	40.54	44.02	46.06	46.26
Rated Input Speed	rpm	3500	3500	3500	3500
Max. Input Speed	rpm	4685	5968	8304	8988
Backlash	°	<30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	%	94	94	94	94
Inertia	10 ⁻⁶ kg m ²	106	56	33	21
Load Capacity	kg	400			
Wheel Material		Vulkollan			
Ambient Temperature	°C	-15...+90			
Protection Class		IP54			



ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: ± 10% 4.5kg
06 updated specifications	Kolev_I	02.05.2024	Date	Name
05 sun depth changed	Kolev_I	31.01.2024	Drawn	11.09.2019 Rehse_P
04 Load capacity updated	Micheli_M	30.06.2020	Reviewed	16.09.2019 Naubert_A
03 specifications updated	Micheli_M	31.03.2020	Released	16.09.2019 Naubert_A
02				
REV	Rev. Text	Name	Date	

PLUG & DRIVE

06200363

State: Released

WD20050-56xx-80X

Rev: 06

Scale: 1 : 2

A3 Page 1