


DIMENSION (UNIT : mm)



Product specification	
Item	Contents
Rubber	JIS K 6251
Hardness	H _a 65±5

Reference		
Item		Contents
Static Spring Rate	Compression	920 N/mm
	Max. Load	740 N
	Shearing	150 N

Special mention

The RoHS directive prohibition material is not used for the material of this product. (the adhesive and the surface treatment are contained.)

				 Nanotec [®] PLUG & DRIVE	SCALE FREE	APVD			DÄMPFER FÜR ANBAUFLANSCH	
					X ±0.5	CHKD				
1	Drawing updated	19.04.10	J.W.		1PL ±0.2	DRN		14.10.2007		DWG.NO
REV	DESCRIPTION	DATE	APVD	ZD-DF56	2PL ±0.1	SIGNATURE		DATE		ZD-DF56
					ANGLE ±30'					