



WHEEL DRIVE SPECIFICATION

	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
Reduction Ratio xx	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
No. of Stages	2			
Rated Output Torque	Nm 19.2	24.6	28.6	29.1
Max. Output Torque	Nm 32.9	39.4	39.4	39.4
Rated Input Speed	rpm 3500	3500	3500	3500
Max. Input Speed	rpm 4685	5968	8304	8988
Backlash	° <30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	% 94	94	94	94
Inertia	10 ⁻⁶ kg m ² 70	37	22	14
Load Capacity	kg 400			
Wheel Material	Vulkollan			
Ambient Temperature	°C -15...+90			
Protection Class	IP54			

04

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 4.8kg	
04	Load capacity updated	Micheli_M	30.06.2020	Drawn	06.09.2019
03	specifications updated	Micheli_M	31.03.2020	Reviewed	16.09.2019
02	First Released			Released	16.09.2019
01	First Released				
REV	Rev. Text	Name	Date		
				WD16050-56xx-80E	
				06200336	
				State: Released Rev: 04 CONFIDENTIAL	

Scale: 1 : 2
A3 Page 1