



WHEEL DRIVE SPECIFICATION

		11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
Reduction Ratio xx		11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
No. of Stages		2			
Rated Output Torque	Nm	19.2	24.6	28.6	29.1
Max. Output Torque	Nm	32.9	39.4	39.4	39.4
Rated Input Speed	rpm	3500	3500	3500	3500
Max. Input Speed	rpm	4685	5968	8304	8988
Backlash	°	<30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	%	94	94	94	94
Inertia	10 ⁻⁶ kg m ²	70	37	22	14
Load Capacity	kg	400			
Wheel Material		Vulkollan			
Ambient Temperature	°C	-15...+90			
Protection Class		IP54			

03

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Date		Name	Weight: 4.0kg
				Drawn	09.09.2019	Rehse_P	WD16050-56xx-80X
03	Load capacity updated	Micheli_M	30.06.2020	Reviewed	16.09.2019	Naubert_A	
02	specifications updated	Micheli_M	31.03.2020	Released	16.09.2019	Naubert_A	
01	First Released						06200355
REV	Rev. Text	Name	Date			State: Released	Rev: 03

Scale: 1 : 2
A3 Page 1

CONFIDENTIAL