



**WHEEL DRIVE SPECIFICATION**

	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
Reduction Ratio xx	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
No. of Stages	2			
Rated Output Torque	Nm 19.2	24.6	28.6	29.1
Max. Output Torque	Nm 32.9	39.4	39.4	39.4
Rated Input Speed	rpm 3500	3500	3500	3500
Max. Input Speed	rpm 4685	5968	8304	8988
Backlash	° <30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	% 94	94	94	94
Inertia	10 <sup>-6</sup> kg m <sup>2</sup> 85	45	27	17
Load Capacity	kg 400			
Wheel Material	Vulkollan			
Ambient Temperature	°C -15...+90			
Protection Class	IP54			

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 5.2kg
			Date	Name
			Drawn 21.06.2021	Rehse_P
			Reviewed 22.10.2021	Rehse_P
			Released 22.10.2021	Rehse_P
REV	Rev. Text	Name	Date	

Scale: 1 : 2  
A3 Page 1



WD18050-56xx-95F  
06200371  
State: Released Rev: 00 CONFIDENTIAL