




Front view and mounting




Side view



Rear view



SPECIFICATION	CONNECTION		BIPOLAR	
	UNIPOLAR OR BIPOLAR-1 WINDING		SERIAL	PARALLEL
VOLTAGE (VDC)	6.0			
AMPS/PHASE	1.2		0.85	1.7
RESISTANCE/PHASE (Ohms)@25°C	5.0±15%		10±15%	2.5±15%
INDUCTANCE/PHASE (mH) @1KHz	11.6±20%		46.4±20%	11.6±20%
HOLDING TORQUE (Nm) [lb-in]	0.75 [6.637]		1.06 [9.381]	1.06 [9.381]
DETTENT TORQUE (Nm) [lb-in]	0.0225 [0.199]			
STEP ANGLE (°)	0.9			
STEP ACCURACY (NON-ACCUM)	±5%			
ROTOR INERTIA (Kg-m <sup>2</sup> ) [lb-in <sup>2</sup> ]	2.75x10 <sup>-5</sup> [0.094]			
WEIGHT (Kg) [lb]	0.65 [1.433]			




TYPE OF CONNECTION (EXTERN)	BIPOLAR				MOTOR	
	UNIPOLAR	1WINDING	SERIAL	PARALLEL	LEADS	WINDING
A ---	A ---	A ---	A ---	RED	A	
COM ---	COM ---	COM ---	COM ---	RED/WHT		
A\ ---	A\ ---	A\ ---	A\ ---	BLK/WHT	A\	
B ---	B ---	B ---	B ---	BLK	B	
COM ---	COM ---	COM ---	COM ---	GRN		
B\ ---	B\ ---	B\ ---	B\ ---	GRN/WHT	B\	
				YEL/WHT		
				YEL		

TEMPERATURE RISE: MAX.80°C (MOTOR STANDSTILL; FOR 2 PHASE ENERGIZED)	AXIAL-FORCE Fa (N)	Fa=10	
AMBIENT TEMPERATURE -10°~ 50°C [14°F ~ 122°F]	DISTANCE a (mm)	5	10 15 20
INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY)	RADIAL-FORCE Fr (N)	130	90 70 52
INSULATION CLASS B 130° [266°F]			AXIAL RADIAL
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)	SHAFT PLAY (mm)	0.075	0.025
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)	AT LOAD MAX: (N)	10	5.0

FULL STEP 2 PHASE-Ex., WHEN FACING MOUNTING END (X)

STEP	A	B	A\	B\	CCW	CW
1	+	+	-	-	↓	↑
2	-	+	+	-	↓	↑
3	-	-	+	+	↓	↑
4	+	-	-	+	↓	↑



REV	DESCRIPTION	DATE	APVD	NANOTEC:	SCALE FREE	APVD	S.H.a.	15.01.07	STEPPING MOTOR
				ST5709S1208	X ±0.5 1PL ±0.2 2PL ±0.1 ANGLE ±30'	CHKD			
						DRN	J.W.	05.07.06	DWG.NO
						SIGNATURE		DATE	ST5709S1208