




Front view and mounting



Side view




Rear view



SPECIFICATION	CONNECTION		BIPOLAR	
	UNIPOLAR OR BIPOLAR-1 WINDING		SERIAL	PARALLEL
VOLTAGE (VDC)	3.4			
AMPS/PHASE	2.0		1.41	2.83
RESISTANCE/PHASE (Ohms)@25°C	1.7±15%		3.4±15%	0.85±15%
INDUCTANCE/PHASE (mH) @1KHz	3.6±20%		14.4±20%	3.6±20%
HOLDING TORQUE (Nm) [lb-in]	0.74 [6.549]		1.05 [9.292]	1.05 [9.292]
DETENT TORQUE (Nm) [lb-in]	0.0294 [0.261]			
STEP ANGLE (°)	1.8			
STEP ACCURACY (NON-ACCUM)	±5%			
ROTOR INERTIA (Kg-m ²) [lb-in ²]	0.29x10 ⁻⁴ [0.099]			
WEIGHT (Kg) [lb]	0.71 [1.566]			
TEMPERATURE RISE: MAX.80°C (MOTOR STANDSTILL; FOR 2 PHASE ENERGIZED)				
AMBIENT TEMPERATURE -10°~ 50°C [14°F ~ 122°F]				
INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY)				
INSULATION CLASS B 130° [266°F]				
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)				
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)				

PERMISSIBLE RADIAL+AXIAL FORCE




	AXIAL-FORCE Fa (N)			
	Fa=10			
DISTANCE a (mm)	5	10	15	20
RADIAL-FORCE Fr (N)	130	90	70	52
		AXIAL	RADIAL	
SHAFT PLAY (mm)		0.075	0.025	
AT LOAD MAX: (N)		10	5.0	

UNIPOLAR	TYPE OF CONNECTION (EXTERN)			MOTOR	
	1WINDING	BIPOLAR SERIAL	BIPOLAR PARALLEL	LEADS	WINDING
A	A	A	A	BLK	A
COM				BLK/WHT	
A\		A\	A\	GRN/WHT	A\
B	B	B	B	GRN	B
COM				RED	
B\		B\	B\	RED/WHT	B\
				BLU/WHT	
				BLU	

FULL STEP 2 PHASE-Ex., WHEN FACING MOUNTING END (X)

STEP	A	B	A\	B\	
1	+	+	-	-	CCW
2	-	+	+	-	
3	-	-	+	+	
4	+	-	-	+	CW

WIRING DIAGRAM



				NANOTEC:	SCALE FREE	APVD	<i>S.Ha.</i>	16.01.07	STEPPING MOTOR
				ST5818M2008	X ±0.5	CHKD			
						1PL ±0.2	DRN	<i>J.W.</i>	08.05.06
REV	DESCRIPTION	DATE	APVD		2PL ±0.1	SIGNATURE		DATE	ST5818M2008
					ANGLE ±30'				