




Front view and mounting



Side view




Rear view




SPECIFICATION	CONNECTION	UNIPOLAR OR BIPOLAR		
		BIPOLAR -1 WINDING	SERIAL	PARALLEL
VOLTAGE (VDC)		6.0	8.50	4.25
AMPS/PHASE		1.2	0.85	1.7
RESISTANCE/PHASE (Ohms)@25°C		5.0±15%	10±15%	2.5±15%
INDUCTANCE/PHASE (mH) @1KHz		9.2±20%	36.8±20%	9.2±20%
HOLDING TORQUE (Nm) [lb-in]		0.60 [5.31]	0.848 [7.505]	0.848 [7.505]
DETENT TORQUE (Nm) [lb-in]		0.018 [0.159]		
STEP ANGLE (°)			1.8	
STEP ACCURACY (NON-ACCUM)			±5%	
ROTOR INERTIA (kg-m ²) [lb-in ²]			1.30x10 ⁻⁵ [0.044]	
WEIGHT (kg) [lb]			0.55 [1.213]	
TEMPERATURE RISE: MAX.80°C (MOTOR STANDSTILL; FOR 2 PHASE ENERGIZED)				
AMBIENT TEMPERATURE -10°~ 50°C [14°F ~ 122°F]				
INSULATION RESISTANCE 100 Mohm (UNDER NORMAL TEMPERATURE AND HUMIDITY)				
INSULATION CLASS B 130° [266°F]				
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)				
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)				

PERMISSIBLE RADIAL+AXIAL FORCE



AXIAL-FORCE F _a (N)	F _a =10			
DISTANCE a (mm)	5	10	15	20
RADIAL-FORCE F _r (N)	130	90	70	52
SHAFT PLAY (mm)	0.075			
AT LOAD MAX: (N)	10			


TYPE OF CONNECTION (EXTERN)



FULL STEP 2 PHASE-Ex, WHEN FACING MOUNTING END (X)

STEP	A	B	A\	B\	CCW
1	+	+	-	-	
2	-	+	+	-	
3	-	-	+	+	
4	+	-	-	+	

WIRING DIAGRAM



NANOTEC:

SH5618M1208

REV	DESCRIPTION	DATE	APVD

SCALE	FREE	APVD	S.K.
X	±0.5	CHKD	
1PL	±0.2	DRN	J.W.
2PL	±0.1	SIGNATURE	
ANGLE	±30°	DATE	

STEPPING MOTOR

DWG.NO

SH5618M1208