


Major diameter	[mm]	6.0	0/-0.112
Minor diameter	[mm]	4.7	



Surface specification
DIN ISO 1302

General tolerances
DIN ISO 2768- mK

Work piece edge
DIN ISO 13715

Scale: 2:1

Material: 1.4021

REV	DESCRIPTION	DATE	DRN
2	revise chart	21.06.17	A.S.
1	revise drawing	08.06.17	A.S.



	Name	Date
DRN	J.W.	11.02.2010
CHKD	S.Ha.	11.02.2010

THREADED SPINDLE

ZST6-1-300-1