



Detail cable

Connector: MOLEX 51065-0600
 Contact: MOLEX 50212-8000



Max. Axial Force F_a	N	7
Max. Radial Force F_r ($a_1 = 5$ mm)	N	28
Axial Play	$F_a = 4$ N mm	0.08
Radial Play	$F_r = 4$ N mm	0.02

TYPE OF CONNECTION			
Series	Pin No.	Wire Col.	Winding
A	1	BK	
A\	3	GN	
B	4	RD	
B\	6	BU	

MOTOR SPECIFICATION		
Voltage	V DC	2.85
Current per Winding	A	1.5
Resistance per Phase (25°C)	±15% Ω	1.9
Inductance per Phase (1 kHz)	±20% mH	1.9
Holding Torque	Nm	0.18
Step Angle	±5% °	1.8
Rotor Inertia	kg m ²	1.8 × 10 ⁻⁶

GENERAL MOTOR SPECIFICATION		
Ambient Temperature	°C	-20 ... 50
Max. Temperature Rise (at standstill - 2 phases energized)	°C	80
Max. Ambient Humidity (non condensing)	%	85
Insulation Class		B
Insulation Resistance	MΩ	100
Dielectric Strength (for 1 min - coil to case)	V AC	500

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715
			Date
			Name
			Drawn 23.06.2021
			Reviewed 02.07.2021
			Released 02.07.2021
REV	Rev. Text	Name	Date

Weight: ~0.2 kg

SCA2818L1504-L

20001088

State: Released Rev: 00 CONFIDENTIAL

A4 Page 1

