







N6-1-1-1, N6-2-1-1
N6-1-3-1, N6-2-3-1
N6-1-4-1, N6-2-4-1
N6-1-10-1, N6-2-10-1




N6-1-2-1, N6-2-2-1
N6-1-5-1, N6-2-5-1
N6-1-13-1, N6-2-13-1



N6-1-1-1, N6-2-1-1
N6-1-3-1, N6-2-3-1
N6-1-4-1, N6-2-4-1
N6-1-10-1, N6-2-10-1



N6-1-2-1, N6-2-2-1
N6-1-5-1, N6-2-5-1




N6-1-13-1, N6-2-13-1

N6-1-1-1, N6-2-1-1 = EtherCAT
N6-1-3-1, N6-2-3-1 = EtherNet/IP
N6-1-4-1, N6-2-4-1 = Modbus TCP
N6-1-10-1, N6-2-10-1 = ProfiNet

N6-1-2-1, N6-2-2-1 = CANopen
N6-1-5-1, N6-2-5-1 = Modbus RTU (RS485)

N6-1-13-1, N6-2-13-1 = IO-Link

Label Detail



* Optional, not included in delivery.

Lot No. Production location

Marking on Label (Letters)	Factory
NCN	Nanotec Electronics (ChangZhou) Co., Ltd.
NBG	Nanotec Electronic Bulgaria EOOD
NDE	Nanotec Electronic GmbH & co. KG

ISO 8015	ISO 1302	ISO 2768 m	ISO 13715	Material:	Weight: ± 10% 0.2 kg
			Date	N6-x-x-1	
			Drawn 14.05.2024		
			Reviewed 27.01.2026		
			Released 27.01.2026	20002465	
01	CR_2026-0006	Schneid_A	05.02.2026	State: Released	
REV	Rev. Text	Name	Date	Rev: 01 CONFIDENTIAL	

