









				General tolerances ISO 2768-m		Work piece edges DIN 6784	Scale:		
							Material:		
							Surface:		
					Datum	Name			
				DRN	2025/10/14	L X			
				CHKD	2025/10/14	X T			
				APVD	2025/10/14	GYQ			