









N6-1-2-1-S, N6-2-2-1-S
N6-1-5-1-S, N6-2-5-1-S

N6-1-13-1-S, N6-2-13-1-S



N6-1-1-1-S, N6-2-1-1-S
N6-1-3-1-S, N6-2-3-1-S
N6-1-4-1-S, N6-2-4-1-S
N6-1-10-1-S, N6-2-10-1-S


N6-1-2-1-S, N6-2-2-1-S
N6-1-5-1-S, N6-2-5-1-S
N6-1-13-1-S, N6-2-13-1-S

N6-1-1-1-S, N6-2-1-1-S = EtherCAT
N6-1-3-1-S, N6-2-3-1-S = EtherNet/IP
N6-1-4-1-S, N6-2-4-1-S = Modbus TCP
N6-1-10-1-S, N6-2-10-1-S = ProfiNet

N6-1-2-1-S, N6-2-2-1-S = CANopen
N6-1-5-1-S, N6-2-5-1-S = Modbus RTU (RS485)

N6-1-13-1-S, N6-2-13-1-S = IO-Link

Label Detail



Lot No. Production location

* Optional, not included in delivery.

Marking on Label (Letters)	Factory
NCN	Nanotec Electronics (ChangZhou) Co., Ltd.
NBG	Nanotec Electronic Bulgaria EOOD
NDE	Nanotec Electronic GmbH & co. KG

ISO 8015	ISO 1302	ISO 2768 m	ISO 13715	Material:	Weight: ± 10% 0.2 kg
			Date	Name	
			Drawn	14.05.2024	Schneid_A
			Reviewed	27.01.2026	Reith_S
			Released	27.01.2026	Reith_S
01	CR_2026-0006	Schneid_A	05.02.2026		
REV	Rev. Text	Name	Date		

N6-x-x-1-S		Scale: 1 : 1
20003425		A3 Page 1
State: Released	Rev: 01	CONFIDENTIAL