

MOTOR SPECIFICATION		
Voltage	V DC	2.1
Current per Winding	A	2.8
Resistance per Phase (25°C) ±15%	Ω	0.78
Inductance per Phase (1 kHz) ±20%	mH	1.8
Holding Torque	Nm	0.6
Step Angle ±5%	°	1.8
Rotor Inertia	kg m²	12 x10^{-6}

TYPE OF CONNECTION		
Bipolar	Pin No.	Winding
A	1	
A\	3	
B	4	
B\	6	



Max. Axial Force Fa		N	15
Max. Radial Force Fr (a2 = 20 mm)		N	75
Axial Play	Fa = 4.0 N	mm	0.08
Radial Play	Fr = 4.0 N	mm	0.02

GENERAL MOTOR SPECIFICATION		
Ambient Temperature	°C	-20 ...50
Max. Temperature Rise (at standstill - 2 phases energized)	°C	80
Max. Ambient Humidity (non condensing)	%	85
Insulation Class		B
Insulation Resistance	MΩ	100
Dielectric Strength (for 1 min - coil to case)	V AC	500

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 0.45 kg

		Date	Name
Drawn		20.12.2018	Schneid_A
Checked		20.12.2018	Knoll_J
Approved		16.10.2019	Reith_S

REV	Rev. Text	Name	Rel. Date
01	change dimension conn.	Schneid_A	16.10.2019

Nanotec® PLUG & DRIVE

SCA5618X2804-B

01200257 -

State: Released | Rev: 01 | P