


MOTOR SPECIFICATION		
Voltage	V DC	4.3
Current per Winding	A	0.8
Resistance per Phase (25°C)	±15% Ω	5.4
Inductance per Phase (1 kHz)	±20% mH	1.5
Holding Torque	Nm	0.03
Step Angle	±5% °	1.8
Rotor Inertia	kg m ²	0.36 × 10 ⁻⁶

GENERAL MOTOR SPECIFICATION		
Ambient Temperature	°C	-10 ... 50
Max. Temperature Rise (at standstill - 2 phases energized)	°C	80
Max. Ambient Humidity (non condensing)	%	85
Insulation Class		B
Insulation Resistance	MΩ	100
Dielectric Strength (for 1 min - coil to case)	V AC	500



TYPE OF CONNECTION			
Bipolar	Pin No.	Wire Col.	Winding
A	1	BK	
A1	2	GN	
B	3	RD	
B1	4	BU	

Max. Axial Force F_a	N	4.0
Max. Radial Force F_r ($a_1 = 5$ mm)	N	30
Max. Radial Force F_r ($a_2 = 20$ mm)	N	8
Axial Play $F_a = 10$ N	mm	0.075
Radial Play $F_r = 5.0$ N	mm	0.025

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Replacement for drawing from 02.06.06	Weight: ±10% 0.080 kg
			Date	Name	ST2018M0804-A
			Drawn	Schneid_A	
			Reviewed	Reith_S	
			Released	Reith_S	
07	modified prod. process	Schneid_A	06.12.2023	20002134	
REV	Rev. Text	Name	Date	State: Released	Rev: 07 CONFIDENTIAL

