




MOTOR SPECIFICATION								
PD6-EB80xx-x-65-2	SD-M	SD-E	MD-M	MD-E	LD-M	LD-E	CD-M	CD-E
Motor Length "A"	mm	134	155	170	190			
No. of Poles		8						
Rated Voltage	V DC	48						
Min. Operating Voltage	V DC	12						
Max. Operating Voltage	V DC	57.6						
Current - Rated / Peak	A	6.9 / 20	14 / 40	18.75 / 65	25 / 75			
Torque - Rated / Peak	Nm	0.9 / 2.5	1.7 / 5	2.25 / 6.5	3 / 9			
Torque Constant	Nm/A	0.13	0.12	0.12	0.12			
Power Rated	W	283	534	706	940			
Speed - No Load / Rated ±10%	rpm	4100 / 3000	4250 / 3000	4300 / 3000	4250 / 3000			
Rotor Inertia	kg m <sup>2</sup>	54.4 x 10 <sup>-6</sup>	102 x 10 <sup>-6</sup>	136 x 10 <sup>-6</sup>	190 x 10 <sup>-6</sup>			
Multiturn Encoder Resolution	bit	17	-	17	-	17	-	-
Singleturn Encoder Resolution	bit	16	12	16	12	16	12	12
Weight	kg	~2.0	~2.7	~3.1	~3.8			



X3	CANopen IN
M12/ 5-Pole / A-Coding / male	

X4	CANopen OUT
M12/ 5-Pole / A-Coding / female	
Pin No.	Function
1	CAN_SHLD
2	+UB Logic (24V)
3	GND
4	CAN+
5	CAN-

X5	Brake OUT
M8/ 3-Pole / A-Coding / female	
PIN No.	Function
1	Brake
3	Brake GND
4	N.C.

X6	Mini-USB
----	----------

X1	POWER
M12 / 4-Pole / L-Coding / male	
Pin No.	Function
1	+UB
2	+UB
3	GND
4	GND

X2	IO
M12 / 12-Pole / A-Coding / male	
Pin No.	Function
1	GND
2	Input 1 (+5V/+24V)
3	Input 2 (+5V/+24V)
4	Input 3 (+5V/+24V)
5	Input 4 (+5V/+24V)
6	Input 5 (+5V/+24V)
7	Input 6 (+5V/+24V)
8	Analog Input (0-10V/0-20mA)
9	Output 1 (open drain)
10	Output 2 (open drain)
11	+5V Voltage Supply (max. 100mA)
12	+UB Logic (24V)

GENERAL MOTOR SPECIFICATION	
Interface	CANOPEN
Ambient Temperature	-10 ... 40 °C
Switch-off Temperature	75 °C
Max. Ambient Humidity (non condensing)	85 %
Protection Class (except shaft outlet)	IP65
Protection Class (shaft outlet)	IP54

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715
			Date
			Name
			Drawn
			28.07.2022
			Schneid_A
			Reviewed
			02.08.2022
			Rehse_P
02	correct pos. USB Con.	Schneid_A	07.09.2022
			Released
			02.08.2022
			Rehse_P
01	added remarks	Rehse_P	17.08.2022
REV	Rev. Text	Name	Date



PD6-EB80xD-x-65-2

20001580

State: Released      Rev: 02      CONFIDENTIAL

A4 Page 1