


DIMENSION (UNIT : mm)



TECHNICAL DATA:

Operating voltage: 24 - 48V DC +/-5%
 Current consumption: < 2mA (when brake is not connected)
 Delay time: 500 ms
 Output voltage: +24V for 500 ms, and then +18V by means of PWM
 Output frequency: 37 kHz
 Operating temperature: -20°C to 85°C

PIN ASSIGNMENT	
PIN NO.	FUNCTION
1	Brake+
2	Brake-
3	VCC(24-48V)
4	GND

				 Nanotec [®] PLUG & DRIVE			APVD	<i>M.G.</i>	2016.8.2	EB-BRAKE DWG.NO EB-BRAKE-48V
							CHKD	<i>L B</i>	2016.8.2	
A	-	2016.11.14	GYQ	Surface specification DIN ISO 1302	General tolerances DIN ISO 2768-ch	Work piece edge DIN ISO 13715	DRN	<i>GYQ</i>	2016.8.2	
REV	DESCRIPTION	DATE	APVD				SIGNATURE	DATE		

A

B

C

D

E

F