


Thread code:UECB	
Thread type	ACME
Major diameter(mm)	3.759...4.044
Minor diameter(mm)	2.504...2.631
Lead	2
Pitch	1
Starts	2

Spring data	
Test length L1(mm)[in]	6.07 [0.24]
Force at L1(N)[lb]	9.71 [2.18]
Spring rate(N/mm)[lb/in]	1.191 [6.801]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale: 5:1	
Datum		Name		Material: POM	
DRN	2020/9/29	X	T	Surface:	
CHKD	2020/9/29		GYQ	axial-compensated nut	
APVD					
					
				LSNUT-AEAC-UECB	
				1	
				A3	
Rev	Description	Date	Name		