



Thread code:UQBN	
Thread type	ACME
Major diameter(mm)	9.779...10.033
Minor diameter(mm)	7.938...8.065
Lead	1.5875
Pitch	1.5875
Starts	1

Spring data	
Test length L1(mm)[in]	12.01[0.47]
Force at L1(N)[lb]	36.13[8.12]
Spring rate(N/mm)[lb/in]	2.699[15.41]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale: 3:1	
Datum		Name		Material: POM	
DRN 2021/11/5		X T		Surface:	
CHKD 2021/11/5		GYQ		axial-compensated nut	
APVD 2021/11/5		P.R.			
				LSNUT-AEAJ-UQBN	
				1	
Rev		Description		Date	

A

B

D

6

5

4

3

3

2

1

6

5

4

3

3

2

1

A

B

D