


A →



Thread code:UEAI	
Thread type	ACME
Major diameter(mm)	3.759...4.013
Minor diameter(mm)	3.200...3.327
Lead	0.3048
Pitch	0.3048
Starts	1

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:	
						Material: POM	
						Surface:	
				Datum		Name	
				DRN		2022/12/16 X T	
				CHKD		2022/12/16 GYQ	
				APVD		2022/12/16 P.R.	
						External linear nut	
						LSNUT-AAAA-UEAI	
						1	
						A3	
Rev	Description	Date	Name				

