



Thread code:UKAS	
Thread type	ACME
Major diameter(mm)	6.604...6.858
Minor diameter(mm)	5.555...5.682
Lead	0.79375
Pitch	0.79375
Starts	1

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:		
						Material: TECAFORM AD AF		
						Surface:		
				Datum	Name	axial-compensated nut		
				DRN	2021/3/3			X T
				CHKD	2021/3/3			GYQ
				APVD	2021/3/3			P.R.
				Nanotec PLUG & DRIVE		LSNUT-AFAE-UKAS		
						1		
						A3		
Rev	Description	Date	Name					