



Thread code:UKDE	
Thread type	ACME
Major diameter(mm)	6.604...6.909
Minor diameter(mm)	4.763...4.892
Lead	3.175
Pitch	1.5875
Starts	2

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:			
						Material: TECAFORM AD AF			
						Surface:			
				Datum		Name			
				DRN 2021/3/3		X T			
				CHKD 2021/3/3		GYQ			
				APVD 2021/3/3		P.R.			
						axial-compensated nut			
								LSNUT-AFAE-UKDE	
Rev						Description		Date	Name
									A3