



Thread code UQKE	
Thread type	ACME
Major diameter [mm]	9.398...9.525
Minor diameter [mm]	5.977...6.477
Lead	10.16
Pitch	2.54
Starts	4
Thread per inch	10

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (± 1.4570)	
B	-	25.07.22	X T		Nanotec PLUG & DRIVE	DRN	L W	10.04.2018	THREADED SPINDLE
A	-	18.04.18	L W			CHKD	GYQ	10.04.2018	
REV	DESCRIPTION	DATE	DRN			APVD	P.R.	10.04.2018	