



WHEEL DRIVE SPECIFICATION

	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
Reduction Ratio xx	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
No. of Stages	2			
Rated Output Torque	Nm 19.2	24.6	28.6	29.1
Max. Output Torque	Nm 32.9	39.4	39.4	39.4
Rated Input Speed	rpm 3500	3500	3500	3500
Max. Input Speed	rpm 4685	5968	8304	8988
Backlash	° <30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	% 94	94	94	94
Inertia	10^{-6} kg m ² 85	45	27	17
Load Capacity	kg 400			
Wheel Material	Vulkollan			
Ambient Temperature	°C -15...+90			
Protection Class	IP54			



ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 4.3kg
05 Load capacity updated	Micheli_M	30.06.2020	Date	Name
04 specifications updated	Micheli_M	31.03.2020	Drawn	11.09.2019 Rehse_P
03 Variant table updated	Knoll_J	18.12.2019	Reviewed	16.09.2019 Naubert_A
02 -			Released	16.09.2019 Naubert_A
01 First Released				
REV Rev. Text	Name	Date		
WD18050-56xx-80X				06200359
State: Released				Rev: 05
CONFIDENTIAL				Scale: 1 : 2
				A3 Page 1