



X1
M12/ 5-Pole
L-Coding male

X2
M12/ 8-Pole
A-Coding male



Missing dimensions see in Step File

ISO 8015	ISO 1302	ISO 2768 mK	ISO 13715	Material:	Weight: ~1.7 kg
			Date	WD10030-42xx-50-E4	
			Name		
			Drawn	20002147	
			Reviewed	Scale: 1 : 2	
			Released	A3 Page 1	
				State: Released	
				Rev: 00	
				CONFIDENTIAL	

		12	15	21	26	
System	WD10030-42xx-50-E4					
	Output Torque - Rated / Max.	Nm	4.88 / 14.64	6.41 / 19.23	8.56 / 25.68	10.63 / 26.28
	Speed Rated	m/s	1.6	1.2	0.9	0.7
	Load Capacity	kg	200			
	Inertia (on motor shaft)	kg m ² x 10 ⁻⁶	26.5	24.9	23.8	23.3
Motor	Protection Class	IP54				
	Rated Voltage	V DC	48			
	Current - Rated / Peak	A	5.9 / 17.7		5.9 / 14.6	
	Speed Rated	rpm	3500			
	No. of Poles		20			
Mechanical	Gearbox Reduction Ratio		11.76 (576/49)	15.45 (12996/841)	20.64 (1197/58)	25.62 (333/13)
	Mechanical Efficiency	%	~83			
	Backlash Max.	°	1			
Encoder	Wheel Material		Vulkollan 92 Shore A			
	Operating Voltage	V DC	9 ... 30			
	Resolution	bit	17			
	Interface		absolute			
Envir.	Ambient Temperature	°C	-15 ... +40			
	Ambient Humidity Max. (non condensing)	%	85			

