



Thread code:TSGA	
Thread type	Trapezoidal
Major diameter(mm)	10.500 Min
Minor diameter(mm)	7.000...7.315
Lead	6
Pitch	3
Starts	2

Spring data	
Test length L1(mm)[in]	12.01[0.47]
Force at L1(N)[lb]	36.13[8.12]
Spring rate(N/mm)[lb/in]	2.699[15.41]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale: 3:1	
Datum				Name		Material: POM	
DRN 2021/8/11				X T		Surface:	
CHKD 2021/8/11				GYQ		axial-compensated nut	
APVD 2021/8/11				P.R.			
						LSNUT-AFAJ-TSGA	
						1	
Rev		Description		Date		Name	
						A3	