



Thread code:UEAI	
Thread type	ACME
Major diameter(mm)	3.759...4.013
Minor diameter(mm)	3.200...3.327
Lead	0.3048
Pitch	0.3048
Starts	1

Spring data	
Test length L1(mm)[in]	6.07 [0.24]
Force at L1(N)[lb]	9.71 [2.18]
Spring rate(N/mm)[lb/in]	1.191 [6.801]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale: 5:1	
Datum		Name		Material: POM	
DRN	2022/12/16	X	T	Surface:	
CHKD	2022/12/16	GY	Q	axial-compensated nut	
APVD				LSNUT-AEAC-UEAI	
Rev	Description	Date	Name	1	
				A3	

