



Thread code: UIAP	
Thread type	ACME
Major diameter(mm)	5.812...6.066
Minor diameter(mm)	4.948...5.075
Lead	0.6096
Pitch	0.6096
Starts	1

				General tolerances ISO 2768-m	Work piece edges DIN 6784	Scale:	
				Datum	Name	Material: POM Surface:	
				DRN	2020/9/11		Axial-compensated nut
				CHKD	2020/9/11		
				APVD	2020/9/11		
				Nanotec [®] PLUG & DRIVE		LSNUT-AGAE-UIAP	
A	-	11.11.20	X T				A3
Rev	Description	Date	Name				